

Calibration Set	HI707-11	HI708-11
Reagent Set	HI707-25 (25 tests)	HI708-25 (25 tests)
Ordering Information	starter kit (reagents for 6 tests), battery, and instructions. HI708 Checker®HC is supplied with sample cuvettes with caps (2), nitrite HR reagent starter kit (reagents for 6 tests), battery, and instructions.	
	HI707 Checker®HC is supplied with sample cuvettes with caps (2), nitrite LR reagent	
Method	adaptation of the EPA Diazotization method 354.1. The reaction be-tween nitrite and the reagent causes a pink tint in the sample.	Adaptation of the Ferrous Sulfate method. The reaction between nitrite and the reagent causes a greenish-brown tint in the sample.
Weight	64 g (2.3 oz)	
Dimensions	86.0 x 61.0 x 37.5 mm (3.4 x 2.4 x 1.5")	
Auto-off	after ten minutes of non-use and four minutes after reading	after ten minutes of non-use
Battery Type	1.5V AAA (1)	
Environment	0 to 50°C (32 to 122°F); RH max 95% non-condensing	
Light Detector	silicon photocell	
Light Source	LED @ 470 nm	LED @ 575 nm
Accuracy @25°C (77°F)	±20 ppb ±5% of reading	±3 ppm ±5% of reading
Resolution	1 ppb	1 ppm
Range	0 to 600 ppb NO ₂	0 to 150 ppm NO₂
Specifications	HI707 (LR)	HI708 (HR)

111700 (LID)

HI707 · HI708

Nitrite Low Range, and High Range

Handheld Colorimeters

- Easier to use and more accurate than chemical test kits
- Dedicated to a single parameter
- Small size, big convenience
- Ideal for:
 - Aquaculture
 - Aquariums
 - Education
 - Environmental
 - Water quality
 - Wastewater

The HI707 and HI708 Checker®HC Handheld Colorimeters bridge the gap between simple chemical test kits and professional instrumentation. Chemical test kits are not very accurate, while professional instrumentation can cost hundreds of dollars and can be time-consuming to calibrate and maintain. Hanna Checker HC's are accurate, affordable, and easy to use.

To begin measurements, first zero the instrument with your water sample. Next, add the reagent. Last, place the vial into the Checker HC, press and hold the button for 3 seconds to start reaction timer. The reading will be taken automatically and the results displayed. It's that easy.

The contoured style of the Checker HC fits in your palm and pocket perfectly and the large LCD is easy to read. The auto shutoff feature assures the battery life will not be drained if you forget to turn it off.

C---!6!--4!---

111707 (LD)